

FISA INFORMATII AAP

Solicitant

Firma				Persoana de contact	
Adresa de livrare				Telefon	
Cod postal		Oras		Fax	
Nr. Inreg.				e-mail	

Specificatii Ansamblu Arbore Principal (daca informatiile lipsesc – lasati necompletat)

Marca AAP		Marca M/U		Serie OEM	
Model AAP		Model M/U			
Viteza max (rpm)		Putere (kW)		Numar Poli	
Conul sculei		Curent (A)		Voltaaj (V)	
Ungere	☐ Vaselina ☐ Aer-ulei ☐ Ceata ulei			Desen./Desen ansamblu disponibil	☐ Da ☐ Nu

Motivul trimerii pentru Service

☐ Blocat	☐ Vibratii	☐ Temperatura	☐ Senzori	☐ Prindere scula
☐ Defect de rulment	☐ Bataie	☐ Conul arborelui	☐ Zgomot	☐ Rot neuniforma.
☐ Precizie	☐ Jocuri	☐ Motor	☐ Finisare supraf	☐ Altele/Preventiva

Constructia AAP (o singura varianta)

Aplicatie (o singura varianta)

☐ AAP complet ☐ Arbore drept ☐ Spate arb.liber	☐ Rectificare plana ☐ Centru de prelucrare ☐ Rectificare fara centre ☐ Strung ☐ Rectificare interioara ☐ Cap de danturat ☐ AAP de lucru ☐ Altele
---	---

Antrenare (o singura varianta)

Tip montaj (o singura varianta)

Orientare (o singura varianta)

☐ Cureau / Directa ☐ Integrata	☐ Cartus ☐ Bloc	☐ Orizzontal ☐ Vertical
--	---	---

Codificare rulmenti- fata

Buc.

Codificare rulmenti - spate

Buc.

Solicitare returnare rulmenti

Este disponibil AAP de

Timpul de service dorit (zile lucratoare)

☐ Da ☐ Nu	☐ Da ☐ Nu	
---	---	--

Reparatii anterioare AAP

Cand		De cine		Comentarii	
------	--	---------	--	------------	--

Informatii aditionale

--